


# GENERA.



Creation made reliable.

GB

## G3 ALL IN ONE SYSTEM



All-in-One. Automated. Compact.

The powerful technologies of the G2 and F2 have now been integrated into one compact machine. For the first time ever, users can take a digital part file to a fully washed and post-cured part, all in one machine. G3 can be preconfigured for 40, 70, or 100  $\mu\text{m}$  pixel size resolutions using the same powerful 4K 385nm DLP light engine found in the G2. Print with the same flexibility as the G2 using the open material vat resin system and GENERA's ever-expanding material database. Parts are automatically cleaned after printing with our non-flammable Genera Clear3d cleaning fluid in the wash station with integrated stirrer. Final post-curing is completed in the high-powered and homogenous UV LED post-curing chamber that is temperature programable with optional inert atmosphere. Print, wash, and post-cure. All with the G3.

### HARD FACTS

<b>Print volume</b> <b>@40/70/100 <math>\mu\text{m}</math></b>	<b>Available preset</b> <b>pixel sizes</b>
x: 153/268/384 mm	40 $\mu\text{m}$ or
y: 87/153/216 mm	70 $\mu\text{m}$ or
z: 320 mm	100 $\mu\text{m}$

<b>Wavelength</b>	<b>Speed</b>
385 nm DLP	Up to 3 mm/min*

<b>Light intensity</b>	<b>4K Resolution</b>
max. 25 mW/cm <sup>2</sup>	(3840 x 2160)

**Active carbon filter for odor reduction**

**Fully automated post-processing**  
(1 Build Job)

**Non-flammable cleaning fluid**  
(Genera Clear3d)

**High power and uniform LED curing chamber @ 405 nm**

**Post-curing in inert atmosphere with part tempering**

**Intelligent database for printing, post-processing and documentation**

\*depending on material and vat system



G3 ALL IN ONE SYSTEM



The powerful technologies of the G2 and F2 have now been integrated into one compact machine. For the first time ever, users can take a digital part file to a fully washed and post-cured part, all in one machine. G3 can be preconfigured for 40, 70, or 100 µm pixel size resolutions using the same powerful 4K 385nm DLP light engine found on the G2. Print with the same flexibility as the G2 using the open material vat resin system and Genera's ever-expanding material database. Parts are automatically cleaned after printing with our non-flammable Genera Clear3d cleaning fluid in the wash station with integrated stirrer. Final post-curing is completed in the high-powered and homogenous UV LED post-curing chamber that is temperature programable with optional inert atmosphere flooding.

Print, wash, and post-cure. All with the G3.

HARD FACTS

**Print volume**  
@40/70/100 µm  
x: 153/268/384 mm  
y: 87/153/216 mm  
z: 320 mm

**Available preset pixel sizes**  
40 µm or  
70 µm or  
100 µm

**Wave length**  
385 nm DLP

**Speed**  
Up to 3 mm/min\*

**Light intensity**  
max. 30 mW/cm<sup>2</sup>

**4K Resolution**  
(3840 × 2160)

**Active carbon filter for odor reduction**

**Fully automated post-processing**  
(1 Build Job)



**Non-flammable cleaning fluid**  
(Genera Clear3d)

**High power and uniform LED curing chamber @ 405 nm**

**Post-curing in inert atmosphere with part tempering**

**Intelligent database for printing, post-processing and documentation**

\*depending on material and vat system



MACHINE COMPONENTS

- 1 Print/post-processing diagnostic sensors
- 2 Automatic handling system for platforms
- 3 Heated build platform
- 4 Resin temperature sensor
- 5 Resin level sensor
- 6 Wash fluid level sensor
- 7 Special heatable vat system
- 8 4K 385 nm DLP light engine
- 9 Glove-free process with fully automated post-processing
- 10 Integrated stirrer and protection for delicate and efficient cleaning of green parts
- 11 Heating unit (part drying and tempering)
- 12 LED post-curing chamber
- 13 LED for status information
- 14 Resin tank and lightproof, automated resin dispensing system for high throughput production
- 15 Secure, fully enclosed, air-filtered machine
- 16 Human Machine Interface (HMI) with machine control, part preview, and print-/post-process progress

